

# **DUPLI-COLOR STYRO PRIMER**

Ord.-no.: 707278, 720765

## **Technical Information**



Fast-drying spezial primer to seal all polystyrene surfaces before painting with solvent-conaining top-coats. After using this protective primer you can lacquer the object with any DUPLI-COLOR synthetic, nitro-combi or acrylic spray paint. Indispensable for stand constructors, decorators etc., but also for handicraft work at home or in courses and seminars.

### **Quality & properties**

- Netting Primer which creates a barricade between polystyrene and dissolving, solventbased paints
- · Good flow, smooth surface
- Quick-drying

### Physical & chemical data

- Base: Special resinColourname: beige
- Smell: Characteristic
- Degree of gloss: mat, 10 ±2 GU
- Efficiency:
  - 400 ML 0.6 0.8 m<sup>2</sup>
  - $\circ$  150 ML  $0.2 0.3 \text{ m}^2$
- Dry to touch: 30 min
- Overcoatable: 3 h
- Surfaces: handicrafts and decorative items
- Minimum Working Temperature: 10 °C
   Maximum Working Temperature: 25 °C
- Maximum Working Temperature: 25 °C
- Vapour pressure: 8300/20 bar
- Storage stability: 10 y
- Content:
  - 400 ML
  - 150 ML

## How to use

- The ground has to be clean, dry and free from fat.
- · Mask off areas not to be painted.
- · Before use, shake the can for approx. 2 minutes.
- Spray from a distance of approx. 20 cm several thin cross-coats. To achieve a sufficient protection, we
  recommend to apply at least 3 cross-coats. In order to grant an optimal protection, it is necessary to have an
  all-over coating without gaps. Apply an additional cross-coat onto rough, open polystyrene surfaces,
  especially cut and waste edges.
- After drying you may apply any DUPLI-COLOR top coat you desire. Apply the first paint layer in a light, nebular way.

## **Environmentally sound**

European Aerosols is committed to apply formulations without restricted or critical ingredients and to achieve best possible performance. The caps and packagings are made of recyclable material.

#### Disposal

Only the completely emptied cans should be put into the recycling skip or appropriate container for reclaimable refuse. Cans which are not empty should be disposed off as "special refuse".

#### Marking/Labelling

All products made by European Aerosols comply with the actual labelling regulations according to Preparation Guideline 1999/45/EG. All aerosols correspond to TRGS 200 and TRG 300 as well as to aerosol guideline 75/324/EWG in the actually valid version.

For any further technical questions call our hotline +49 (0) 62 66 75-266 from Monday to Thursday from 9 h a.m. to 3 h p.m. or on Friday until 12 h p.m.

As of August 18, 2022 – This release replaces all eventually earlier issued versions.

European Aerosols GmbH, Kurt-Vogelsang-Straße 6, 74855 Haßmersheim - info-de@european-aerosols.com European Aerosols B.V., Wolfraamweg 2, NL-8471 XC Wolvega - info-nl@european-aerosols.com